

# Rittal – The System.

Faster – better – everywhere.



## VX 8660.080

Obrobe podnožja/podstavka,  
stranice, za VX sistem podnožja/  
podstavka, nerjavno jeklo

State: 23.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8660.080 - Obrobe podnožja/podstavka, stranice, za VX sistem podnožja/podstavka, nerjavno jeklo Nova različica

Za zaključek stranic podnožja/podstavka se uporabljajo obrobe iz nerjavnega jekla.



## Features

|                        |  |
|------------------------|--|
| Št. Modela             | VX 8660.080  |
| Material               | Nerjavno jeklo 1.4301 (AISI 304)   |
| Površinska obdelava    | Brušeno, zrnatost 400  |
| Obseg dobave           | Sestavni deli  |
| Opomba                 | Komponent iz sistema podnožja/podstavka 1. generacije ni mogoče kombinirati s komponentami iz sistema podnožja/podstavka 2. generacije |
| Mere                   | Višina: 200 mm   |
| Primerno za            | Vrsta ohišja: VX<br>VX SE<br>TS<br>PC<br>Globina: = 400 mm   |
| Tipska ocena po UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12  |
| Paketi                 | 2 pc(s).   |

# Features

---

|                           |   |
|---------------------------|---|
| Neto teža                 | 1,9 kg  |
| Bruto teža                | 2,113 kg  |
| Carinska tarifna številka | 94039910  |
| ETIM 9                    | EC000721  |
| ETIM 8                    | EC000721  |
| ECLASS 8.0                | 27182003  |
| Opis izdelka              | VX base/plinth trim panel, sides, H: 200 mm, for D: 400 mm, stainless steel, 1.4301 |

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|