

# Rittal – The System.

Faster – better – everywhere.



## TS 8800.540 Cable duct

State: 11.5.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8800.540 - Cable duct for vertical TS section

For mounting on the vertical enclosure section, on two bayed enclosure sections in the vicinity of baying.



## Features

Model No.	TS 8800.540
Design	Width 100 mm, for assembly on two bayed enclosure sections in the baying area.
Benefits	<p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed for combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p>
Material	Hard PVC Flame-resistant, self-extinguishing
Colour	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5,5 mm
Slot width	4,5 mm
Note	Can be shortened for other enclosure sizes.

# Features

Dimensions	Width: 100 mm Height: 1,600 mm Depth: 80 mm
To fit	Enclosure type: TS VX SE PC IW Height: ≤ 1,800 mm
Operating temperature range	60 °C
Packs of	4 pc(s).
Net weight	8.192
Gross weight	8.623
Customs tariff number	73269098
EAN	4028177238008
ECLASS 8.0	27400703

# Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---