
Rittal – The System.

Faster – better – everywhere.





TS 8800.753 Cable duct

State: 17.11.2025 (Source: rittal.com/si-sl)



TS 8800.753 - Cable duct

With special DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates. Nominal break points on the bars and on the cable duct base.





Features

nounting plates mounting on VX system punchings
,
special DIN punchings for direct mounting on the enclosure ion or on surfaces such as mounting plates. Nominal break ts on the bars and on the cable duct base.
d PVC ne-resistant, self-extinguishing perature resistant to +60 °C
lar to RAL 7030
e duct with cover
nm
nm
special DIN punchings for direct mounting on the enclosure ion or on surfaces such as mounting plates e mounting plate is installed flush with the enclosure frame at ear (installation position ±0 mm), the horizontally mounted e ducts are aligned with the cable ducts mounted on the osure section.

© Rittal 2025

Features

Dimensions	Width: 80 mm Depth: 80 mm Length: 2,000 mm
Packs of	12 pc(s).
Net weight	17.88
Gross weight	18.72
Customs tariff number	39259020
EAN	4028177445475
ETIM 9	EC000012
ECLASS 8.0	27400703

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3