


Rittal – The System.

Faster – better – everywhere.



GA 9104.210

Lita aluminijasta ohišja GA

State: 3.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



GA 9104.210 - Lita aluminijasta ohišja GA

Lito aluminijasto ohišje z zaključnim premazom. Razred zaščite IP 66.



Features

Št. Modela	GA 9104.210
Material	Ohišje: lito aluminijasto Pokrov: lito aluminijasto, gumeno CR tesnilo po celotnem obodu
Površinska obdelava	Teksturirana barva
Barva	RAL 7001
Obseg dobave	Ohišje s pokrovom Vijaki pokrova, pritrjeni Vijaki za pritrnitev podpornih tirnic Vijak za priklop ozemljitvenega PE vodnika
Protection category NEMA	NEMA 4
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 75 mm Višina: 80 mm Globina: 58 mm
Osnovni material	Cast aluminium
Paketi	1 pc(s).
Neto teža	0,3 kg
Bruto teža	0,33 kg
Carinska tarifna številka	84879090

Features

ETIM 9	EC000261
ECLASS 8.0	27180101
Opis izdelka	GA Cast aluminium enclosure, WHD: 75x80x57 mm, Cast aluminum, without mounting plate, with cover

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	-----------------------------------------------------------