

Rittal – The System.

Faster – better – everywhere.



SV 9340.430 OM adapterji

State: 3.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.430 - OM adapterji s priključnimi kablji



Features

Št. Modela	SV 9340.430
Zasnova	S priključnim kablom
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	Ogrodje: RAL 7035
Priključni kabli (AWG)	AWG 6
Maks. nazivni tok	65 A
Nazivna delovna napetost	690 V, 3~
Opomba	Tehnični podatki se lahko razlikujejo glede na UL aplikacije.
Električne nazivne vrednosti UL (SCCR)	30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7 65 kA - 480 V, Manual Motor Controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
Za sisteme palic z razmakom med središči	60 mm
Dolžina priključnega kabla	130 mm
Vrsta podporne tirnice	Support frame, 1 x TS 55E
Število polov	3-pole
Mere	Širina: 55 mm Višina: 208 mm

Features

Podporne tirnice količina/višina	1 / 10 mm
Za namestitev zbiralnih sponk	Višina: 5, 10 mm
Podporni okvir (Š x V)	55 mm x 170 mm
Odobritve	UL
Paketi	1 pc(s).
Neto teža	0,34 kg
Bruto teža	0,384 kg
Teža bakra (kg na kos)	0,116
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV OM adaptor, 65 A, 690 V, 3-pole, connection cable AWG 6, WH: 55x208 mm, support frame, support rail TS 55E

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK