

Rittal – The System.

Faster – better – everywhere.



SV 9340.650 OM adapterji

State: 3.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.650 - OM adapterji z vzmetnimi priključki



Features

Št. Modela	SV 9340.650
Zasnova	z vzmetnimi priključki
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	Ogrodje: RAL 7035
Maks. nazivni tok	65 A
Nazivna delovna napetost	690 V, 3~
Za sisteme palic z razmakom med središči	60 mm
Vrsta podporne tirnice	Support frame, 1 x TS 55E, 1 x TS 55D-V
Število polov	3-pole
Podporni okvir	Yes
Opomba za model št.	V skladu s testom odvajanja toplote po standardu IEC 61 439-1 je podprta tokovna nosilnost do 80 A.
Mere	Širina: 55 mm Višina: 272 mm
Priklop okroglih vodnikov	2,5 - 16 mm ²
Podporne tirnice količina/višina	2 / 10 mm
Za namestitev zbiralnih sponk	Višina: 5, 10 mm

Features

Podporni okvir (Š x V)	55 mm x 237 mm
Paketi	1 pc(s).
Neto teža	0,339 kg
Bruto teža	0,377 kg
Teža bakra (kg na kos)	0,059
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV OM adaptor, 65 A, 690 V, 3-pole, tension spring clamp 2,5-16 mm ² , WH: 55x272 mm, support frame, support rail TS 55E, TS 55D-V

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK