

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.660 OM adapterji

State: 12.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.660 - OM adapterji z vzmetnimi priključki



## Features

Št. Modela	SV 9340.660
Zasnova	z vzmetnimi priključki
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	Ogrodje: RAL 7035
Maks. nazivni tok	32 A
Nazivna delovna napetost	690 V, 3~
Za sisteme palic z razmakom med središči	60 mm
Vrsta podporne tirnice	Support frame, 1 x TS 55D
Število polov	3-pole
Mere	Širina: 55 mm Višina: 208 mm
Priklop okroglih vodnikov	1,5 - 6 mm <sup>2</sup>
Podporne tirnice količina/višina	1 / 10 mm
Za namestitev zbiralnih sponk	Višina: 5, 10 mm
Podporni okvir (Š x V)	55 mm x 170 mm
Paketi	1 pc(s).
Neto teža	0,29 kg

## Features

---

Bruto teža	0,315 kg
Teža bakra (kg na kos)	0,027
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm <sup>2</sup> , WH: 55x208 mm, support frame, support rail TS 45D

## Approvals

---

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK