

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.770 OM adapterji

State: 8.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.770 - OM adapterji s priključnimi kabli

## Features

Št. Modela	SV 9340.770
Zasnova	S priključnim kablom
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	Ogrodje: RAL 7035
Priključni kabli (AWG)	AWG 10
Maks. nazivni tok	32 A
Nazivna delovna napetost	690 V, 3~
Opomba	Tehnični podatki se lahko razlikujejo glede na UL aplikacije.
Električne nazivne vrednosti UL (SCCR)	30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7 50 kA - 600 V, Fuse Class K5 max. 35 A, JDDZ/7 65 kA - 600 V, Fuse Class J max. 30 A, JDDZ/7 65 kA - 600 V, Fuse Class K5 max. 30 A, JDDZ/7 50 kA - 480 V, Combination Motor Controller max. 27 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 32 A, NKJH/7
Za sisteme palic z razmakom med središči	60 mm
Dolžina priključnega kabla	165 mm
Vrsta podporne tirnice	Support frame, 1 x TS 45D, PinBlock
Število polov	3-pole
PinBlock	Yes
Podporni okvir	Yes
Mere	Širina: 45 mm Višina: 272 mm
Podporne tirnice količina/višina	1 / 10 mm
Za namestitvev zbiralnih sponk	Višina: 5, 10 mm

# Features

---

Podporni okvir (Š x V)	45 mm x 237 mm
Odobritve	UL
Paketi	1 pc(s).
Neto teža	0,28 kg
Bruto teža	0,32 kg
Teža bakra (kg na kos)	0,077
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV OM adaptor, 32 A, 690 V, 3-pole, connection cable AWG 10, WH: 45x272 mm, support frame, PinBlock, support rail TS 45D

# Approvals

---

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK