

Rittal – The System.

Faster – better – everywhere.



SV 9340.870 Komplet kablov

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.870 - Komplet kablov za OM adapterje z vzmetnim priključnim blokom

Predsestavljene priključni kabli za individualen priklop stikalnih naprav.



Features

Št. Modela	SV 9340.870
Opis izdelka	Predsestavljene priključni kabli za individualen priklop stikalne opreme, nameščene od zgoraj na OM adapterjih z vzmetnimi sponkami.
Material	PVC izolacija Temperaturno odporno do 105 °C Konci žic ultrazvočno zatesnjeni na obeh straneh
AWG	AWG 10 = 5.26 mm ² ± 6 mm ²
Opomba	AWG = American Wire Gauge
Mere	Dolžina: 140 mm
Paketi	15 pc(s).
Neto teža	0,12 kg
Bruto teža	0,13 kg
Teža bakra (kg na kos)	0,006
Carinska tarifna številka	85444290
ETIM 9	EC000839
ECLASS 8.0	27062302
Opis izdelka	SV Cable set, AWG 10, L: 140 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK