


# Rittal – The System.

Faster – better – everywhere.



## SV 9342.004

## Nosilec PLS zbiralnih sponk

State: 14.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.004 - Nosilec PLS zbiralnih sponk

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole.



## Features

Št. Modela	SV 9342.004
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Nazivna delovna napetost	1000 V, 3~
Električne nazivne vrednosti UL (SCCR)	65 kA - 480 V, support spacing 250 mm, PLS 1600 busbars, circuit breaker max. 1200 A, DIVQ/7
Opomba za model št.	Za UL aplikacije je potrebna uporaba osnovne plošče. UL odobritev velja samo v povezavi z AC aplikacijami
Zasnova nosilca zbiralnih sponk	PLS 1600 PLUS
Število polov	4-pole
Za namestitev zbiralnih sponk	PLS 1600
Za model št.	3516.000 3527.000 3528.010 3529.000
Notranja namestitev	Yes
Razmak med središči zbiralnih sponk	60 mm

# Features

---

Odobritve	UL
Paketi	4 pc(s).
Neto teža	2,2 kg
Bruto teža	2,321 kg
Carinska tarifna številka	85469010
ETIM 9	EC001166
ECLASS 8.0	27400607
Opis izdelka	SV Busbar support, PLS 1600, 4-pole, 60 mm bar centre distance, UL design

# Approvals

---

Approvals	ABS Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK