### Rittal – The System.

Faster – better – everywhere.





# SV 9342.324 Connection adaptor expansion set

State: 30.10.2025 (Source: rittal.com/si-sl)



# SV 9342.324 - Connection adaptor expansion set for 4-pole configuration

Single-pole extra set to complement the 3-pole connection adaptor (SV 9342.310/9342.320) for 4-pole configurations.

#### **Features**

| SV 9342.324   |
|---|
| Single-pole extra set to complement the 3-pole connection adaptor for 4-pole configurations.                |
| Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0                             |
| RAL 7035  |
| 1.600 A   |
| 690 V, 1~   |
| 65 kA - 480 V, circuit breaker max. 1200 A, DIVQ/7<br>65 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7       |
| 60 mm   |
| The technical data may vary for UL applications UL approval only applies in conjunction with AC application |
| Single-pole   |
| 9342.320  |
| Width: 85 mm<br>Height: 270 mm  |
| Height: 5, 10 mm  |
| 65 x 27 mm  |
|   |

© Rittal 2025

2

#### **Features**

| Clamping area for laminated copper bars (W x H)                                | 65 x 22 mm    |
|--|---------------|
| Clamping area for laminated<br>copper bars with 10 mm bar<br>thickness (W x H) | 65 x 22 mm    |
| Packs of   | 1 pc(s).      |
| Net weight   | 0.199         |
| Gross weight   | 1.271         |
| Copper weight (kg per piece)   | 0.136         |
| Customs tariff number  | 85369010      |
| EAN  | 4028177536876 |
| ETIM 9   | EC001531      |
| ECLASS 8.0   | 27370304      |

## **Approvals**

| Approvals    | ABS                          |
|--------------|------------------------------|
|              | DNV-GL                       |
|              | Lloyds Register of Shipping  |
|              | UL + C-UL (listed)           |
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |

© Rittal 2025 3