

# Rittal – The System.

Faster – better – everywhere.



## SV 9342.570 Priključni nosilec

State: 25.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.570 - Priključni nosilec za adapterje komponent odklopnika

Predsestavljena, laminirana ploščata bakrena žica za priklop komercialno dostopnih odklopnikov.



## Features

Št. Modela	SV 9342.570
Opis izdelka	Predsestavljena, laminirana ploščata bakrena žica za priklop standardnih kompaktnih odklopnikov.
Material	Elektrolitski baker F20
Opomba	Univerzalna uporaba za stikalne naprave z razliko dimenzij med montažno ravnino in zgornjim robom kontaktne ravni $20 \pm 5$ mm.
Za model št.	9342.500 9342.510 9342.540 9342.550
Laminirana ploščata bakrena oblika	Število lamel: 6 Širina membrane: 9 mm Debelina membrane: 0,8 mm
Primerno za proizvajalca (tip)	ABB (T1, T1 UL, T2, T2 UL) Eaton (NZM1, NZM1 UL, BZM B1) Schneider Electric (NSC100, NSE75, NSE100)
Paketi	3 pc(s).
Neto teža	0,096 kg
Bruto teža	0,103 kg

# Features

---

Teža bakra (kg na kos)	0,032
Carinska tarifna številka	85446010
ETIM 9	EC002270
ECLASS 8.0	27409221
Opis izdelka	SV Connection bracket E-Cu, for circuit-breaker component adaptor, SV 9342500/510/540/550

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---