

Rittal – The System.

Faster – better – everywhere.



SV 9343.050 NH ločilnik

State: 24.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.050 - NH ločilnik z elektromehanskim nadzorom varovalk

Features

Št. Modela	SV 9343.050
Zasnova	For 60 mm busbar systems
Material	Poliamid Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7035/7001
Vpenjalna površina za laminirane bakrene palice	Širina vpenjalnega območja: 20 mm Višina vpenjalnega območja: 5 mm
Za sisteme palic z razmakom med središči	60 mm
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M8
Nazivni obratovalni tok maks.	160 A
Nazivna delovna napetost	690 V, 3~
Za velikost NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 106 mm Višina: 194 mm
Priklop okroglih vodnikov	10 - 95 mm ²
Za namestitev zbiralnih sponk	Višina: 5, 10 mm
Število polov	3-pole
Round conductor cross-section	10 - 95 mm ²

Features

Paketi	1 pc(s).
Neto teža	1,3 kg
Bruto teža	1,311 kg
Teža bakra (kg na kos)	0,2
Carinska tarifna številka	85365080
ETIM 9	EC000249
ECLASS 8.0	27371401
Opis izdelka	SV NH fuse-switch disconnecter, size 00, 160 A, 690 V, 3-pole, screw M8, with electromechanical fuse monitoring

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK