

Rittal – The System.

Faster – better – everywhere.



SV 9343.250

NH ločilnik

State: 15.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.250 - NH ločilnik z elektromehanskim nadzorom varovalk

Features

| | |
|---|---|
| Št. Modela | SV 9343.250 |
| Zasnova | For 60 mm busbar systems |
| Material | Poliamid Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko |
| Barva | Ogrodje: RAL 7035 Pokrov: RAL 7035/7001 |
| Vpenjalna površina za laminirane bakrene palice | Širina vpenjalnega območja: 50 mm Višina vpenjalnega območja: 10 mm |
| Za sisteme palic z razmakom med središči | 60 mm |
| Kabelska vtičnica | Top/bottom |
| Vrsta električne povezave | Screw M10 |
| Nazivni obratovalni tok maks. | 400 A |
| Nazivna delovna napetost | 690 V, 3~ |
| Za velikost NH | 2 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke) |
| Mere | Širina: 210 mm Višina: 298 mm |
| Priklop okroglih vodnikov | 10 - 240 mm ² |
| Za namestitev zbiralnih sponk | Višina: 5, 10 mm |
| Število polov | 3-pole |
| Round conductor cross-section | 10 - 240 mm ² |

Features

| | |
|---------------------------|---|
| Paketi | 1 pc(s). |
| Neto teža | 3,66 kg |
| Bruto teža | 3,71 kg |
| Teža bakra (kg na kos) | 1 |
| Carinska tarifna številka | 85369095 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |
| Opis izdelka | SV NH fuse-switch disconnecter, size 2, 400 A, 690 V, 3-pole, screw M10, with electromechanical fuse monitoring |

Approvals

| | |
|--------------|---|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity Declaration of conformity UK |