


Rittal – The System.

Faster – better – everywhere.



SV 9344.020 NH ločilnik

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.020 - NH ločilnik z elektronskim nadzorom varovalk

Features

| | |
|---|---|
| Št. Modela | SV 9344.020 |
| Zasnova | Za namestitev montažne plošče |
| Material | Poliamid Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko |
| Barva | Ogrodje: RAL 7035 Pokrov: RAL 7035/7001 |
| Vpenjalna površina za laminirane bakrene palice | Širina vpenjalnega območja: 13 mm Višina vpenjalnega območja: 13 mm |
| for mounting plate assembly | Yes |
| Kabelska vtičnica | Top/bottom |
| Vrsta električne povezave | Box terminal |
| Nazivni obratovalni tok maks. | 160 A |
| Nazivna delovna napetost | 400 V - 690 V, 3~ |
| Za velikost NH | 00 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke) |
| Mere | Širina: 106 mm Višina: 194 mm |
| Priklop okroglih vodnikov | 4 - 95 mm ² |
| Število polov | 3-pole |
| z elektronskim nadzorom varovalk | Yes |
| Round conductor cross-section | 4 - 95 mm ² |
| Paketi | 1 pc(s). |

Features

| | |
|---------------------------|---|
| Neto teža | 0,82 kg |
| Bruto teža | 0,837 kg |
| Teža bakra (kg na kos) | 0,15 |
| Carinska tarifna številka | 85369095 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |
| Opis izdelka | SV NH fuse-switch disconnecter, size 00, 160 A, 400-690 V, 3-pole, box terminal, with electronic fuse monitoring, for mounting plate assembly |

Approvals

| | |
|--------------|---|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity Declaration of conformity UK |