

Rittal – The System.

Faster – better – everywhere.



SV 9344.030 NH ločilnik

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.030 - NH ločilnik z elektronskim nadzorom varovalk

Features

Št. Modela	SV 9344.030
Zasnova	Za namestitev montažne plošče
Material	Poliamid Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7035/7001
Vpenjalna površina za laminirane bakrene palice	Širina vpenjalnega območja: 20 mm Višina vpenjalnega območja: 5 mm
for mounting plate assembly	Yes
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M8
Nazivni obratovalni tok maks.	160 A
Nazivna delovna napetost	400 V - 690 V, 3~
Za velikost NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 106 mm Višina: 194 mm
Priklop okroglih vodnikov	10 - 95 mm ²
Število polov	3-pole
z elektronskim nadzorom varovalk	Yes
Round conductor cross-section	10 - 95 mm ²
Paketi	1 pc(s).

Features

Neto teža	0,7 kg
Bruto teža	0,835 kg
Teža bakra (kg na kos)	0,15
Carinska tarifna številka	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Opis izdelka	SV NH fuse-switch disconnecter, size 00, 160 A, 400-690 V, 3-pole, screw M8, with electronic fuse monitoring, for mounting plate assembly

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK