


Rittal – The System.

Faster – better – everywhere.



SV 9344.610 Priključna omarica

State: 9.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.610 - Priključna omarica za NH ločilnike

Za NH ločilnike velikosti 1 do 3 z vijačnimi sponkami. Za neposreden priklop okroglih in laminiranih bakrenih vodnikov.



Features

Št. Modela	SV 9344.610
Opis izdelka	Za neposreden priklop okroglih in sektorskih vodnikov ter laminiranih bakrenih zbiralnih sponk. Primerno za NH ločilnike z vijačnimi sponkami.
Material	Lita medenina
Površinska obdelava	nikljano
Vpenjalna površina za laminirane bakrene palice	Širina vpenjalnega območja: 20 mm Višina vpenjalnega območja: 14 mm
Vrsta električne povezave	Box terminal
Za velikost	1
OUT_COL_CROSS_SECTION_SEC TOR_CONDUCTOR	50 - 150 mm ²
Priklop okroglih vodnikov	35 - 150 mm ²
Round conductor cross-section	35 - 150 mm ²
Paketi	3 pc(s).
Neto teža	0,171 kg
Bruto teža	0,175 kg
Carinska tarifna številka	73182900

Features

ETIM 9	EC001894
ECLASS 8.0	27400609
Opis izdelka	SV Box terminal, for NH fuse-switch disconnecter, size 1 (with screw terminal), round conductor connection 35-150 mm ² , clamping area WH: 20x14 mm
