

# Rittal – The System.

Faster – better – everywhere.



## SV 9345.005 Fuse holders

State: 31.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.005 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

## Features

|                                    |                                                                                                                                                  |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                          | SV 9345.005                                                                                                                                      |
| Material                           | Polyamide<br>Fire protection corresponding to UL 94-V0                                                                                           |
| Colour                             | RAL 7035                                                                                                                                         |
| Connection for round conductor     | AWG 8 - 18                                                                                                                                       |
| For fuse type (class)              | CC                                                                                                                                               |
| Rated operating current max.       | 30 A                                                                                                                                             |
| Rated operating voltage            | 600 V, 3~                                                                                                                                        |
| Fuse standard                      | UL 248-4                                                                                                                                         |
| Note                               | For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports) |
| Test specification                 | UL 4248-1<br>UL 4248-4<br>UL 4248-8                                                                                                              |
| Note on Model No.                  | Not suitable for accommodating fuses 10 x 38 mm to IEC 60 269-2/-4/-6                                                                            |
| Dimensions                         | Width: 54 mm<br>Height: 81 mm                                                                                                                    |
| Connection of round conductors     | 0.75 - 25 mm <sup>2</sup>                                                                                                                        |
| To fit fuses                       | Diameter: 10 mm<br>Length: 38 mm                                                                                                                 |
| Voltage range for indicator lights | 110 - 600 V                                                                                                                                      |
| Electrical ratings UL (SCCR)       | 200 kA - 600 V, Fuse Class CC max. 30 A, JDDZ/7                                                                                                  |

# Features

|                              |               |
|------------------------------|---------------|
| Number of poles              | 3-pole        |
| Packs of                     | 4 pc(s).      |
| Net weight                   | 0.4           |
| Gross weight                 | 0.634         |
| Copper weight (kg per piece) | 0.018         |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177805385 |
| ETIM 9                       | EC001644      |
| ECLASS 8.0                   | 27400613      |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Approvals    | UL + C-UL (listed)                                        |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |