

Rittal – The System.

Faster – better – everywhere.



SV 9345.604 Adapter za odklopnik

State: 3.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.604 - Adapter za odklopnik 4-polni

Features

Št. Modela	SV 9345.604
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Obseg dobave	Priključni trakovi Drсни bloki
Maks. nazivni tok	250 A
Nazivna delovna napetost	690 V, 4~
Električne nazivne vrednosti UL (SCCR)	65 kA - 480 V, circuit breaker max. 250 A, DIVQ/7
Kabelska vtičnica	Top
Za sisteme palic z razmakom med središči	60 mm
Opomba	Kabelska vtičnica: vtičnica stikala ali kot odhodni kabel iz stikalne naprave Tehnični podatki se lahko razlikujejo glede na UL aplikacije.
Število polov	4-pole
Mere	Širina: 140 mm Višina: 310 mm
Za namestitvev zbiralnih sponk	Višina: 5, 10 mm
Primerno za proizvajalca (tip)	ABB (T3S, XT3) Eaton (NZM2-4/250 A) Schneider Electric (NS(X)100, NS(X)160, NS(X)250) Schrack (MC2) Siemens (VL160X, VL160, VL250, 3RV10 63, 3VA12/20/21/22, 3VA61/62)
Paketi	1 pc(s).

Features

Neto teža	2,405 kg
Bruto teža	2,516 kg
Teža bakra (kg na kos)	1,134
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV Circuit-breaker component adaptor, 250 A, 690 V, 4-pole, cable outlet top, with connection straps

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK