

Rittal – The System.

Faster – better – everywhere.



SV 9346.030 NH tanki ločilniki

State: 21.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9346.030 - NH tanki ločilniki



Features

Št. Modela	SV 9346.030
Material	Poliamid, ojačan s steklenimi vlakni Protipožarna zaščita v skladu z UL 94-V0 Kontaki: trd baker s srebrno prevleko
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7001 Ročaj: RAL 7016
Obseg dobave	3 pritrdilne kljuke
Za sisteme palic z razmakom med središči	100 mm
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M8
Nazivni obratovalni tok maks.	160 A
Nazivna delovna napetost	690 V, 3~
Za velikost NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 50 mm Višina: 400 mm
Priklop okroglih vodnikov	2,5 - 95 mm ²
Za namestitev zbiralnih sponk	Višina: 5, 10 mm

Features

Število polov	3-pole
Round conductor cross-section	2,5 - 95 mm ²
Paketi	1 pc(s).
Neto teža	1,18 kg
Bruto teža	1,259 kg
Teža bakra (kg na kos)	0,65
Carinska tarifna številka	85365080
ETIM 9	EC001046
ECLASS 8.0	27371402
Opis izdelka	SV NH slimline fuse-switch disconnecter, size 00, 160 A, 690 V, 3-pole, screw M8, 100 mm

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK