

Rittal – The System.

Faster – better – everywhere.



SV 9350.075

Konektorji zbiralnih sponk

State: 2.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9350.075 - Konektorji zbiralnih sponk

Za povezovanje zbiralnih sponk, brez vrtanja.

Features

| | |
|-----------------------------------|--|
| Št. Modela | SV 9350.075 |
| Opis izdelka | Za povezovanje pravokotnih vodil brez vrtanja. |
| Material | Konzola: St 37, nikljano Kontaktna plošča: E-Cu, nikljano |
| Vrsta povezave | Single connection |
| Za namestitvev zbiralnih sponk | 12 x 5 - 15 x 10 |
| Paketi | 3 pc(s). |
| Neto teža | 0,39 kg |
| Bruto teža | 0,411 kg |
| Teža bakra (kg na kos) | 0,05 |
| PCF na paket (od zibelke do vrat) | 1,6 kg CO2 eq (Cat B) |
| Opomba o kategoriji PCF | Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana |
| Carinska tarifna številka | 85369010 |
| ETIM 9 | EC000713 |
| ECLASS 8.0 | 27400606 |
| Opis izdelka | SV Busbar connector, for E-Cu 12x5-15x10 mm, single connection |

Approvals

| | |
|-----------|---------------------------|
| Approvals | ABS UL + C-UL (listed) |
|-----------|---------------------------|

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK