

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.230

## Connection module

State: 31.1.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.230 - Connection module REM 800-CON

For connecting spatially remote measuring points.

## Features

|                                                                    |                                                                                                                 |
|--------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Model No.                                                          | SV 9393.230                                                                                                     |
| Product description                                                | For connecting spatially remote measuring points.                                                               |
| Supply includes                                                    | 2 connection modules<br>2 bus connectors (left/right)<br>2 shield clamps<br>2 screw terminals<br>2 end brackets |
| Operating temperature range                                        | -10 °C...55 °C                                                                                                  |
| Storage temperature range                                          | -25 °C...70 °C                                                                                                  |
| Ambient humidity (non-condensing)                                  | 5...25 %                                                                                                        |
| Contamination level                                                | 2                                                                                                               |
| IP protection category to IEC 60529                                | IP 20                                                                                                           |
| For mounting on support rails                                      | Yes                                                                                                             |
| Connection of round conductors, fine wire with wire end ferrule    | 0.2 - 1.5 mm <sup>2</sup>                                                                                       |
| Connection of round conductors, fine wire without wire end ferrule | 0.2 - 1.5 mm <sup>2</sup>                                                                                       |
| Connection of round conductors, single-wire                        | 0.2 - 1.5 mm <sup>2</sup>                                                                                       |
| Connection of round conductors, multi-wire                         | 0.2 - 1.5 mm <sup>2</sup>                                                                                       |
| Connection for round conductor                                     | AWG 16 - 24                                                                                                     |
| Packs of                                                           | 2 pc(s).                                                                                                        |
| Net weight                                                         | 0.36                                                                                                            |

## Features

---

|                       |               |
|-----------------------|---------------|
| Gross weight          | 0.366         |
| Customs tariff number | 85389099      |
| EAN                   | 4028177984974 |

## Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|