

# Rittal – The System.

Faster – better – everywhere.



## SV 9613.000

# Adapter za priklop Mini-PLS zbiralnih sponk

State: 24.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9613.000 - Adapter za priklop Mini-PLS zbiralnih sponk

Nazivni tok 63 A/1600 A/250 A, kabelska izhodna odprtina zgoraj/spodaj.

## Features

Št. Modela	SV 9613.000
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035 Ogrodje: RAL 9011
Vpenjalna površina za laminirane bakrene palice (Š x V)	10 x 8 mm
Opomba	Pri tankih žičnih vodnikih je treba uporabljati kabelske čevlje s končnimi tulci.
Kabelska vtičnica	Top/bottom
Nazivna delovna napetost	690 V
Maks. nazivni tok	63 A
Mere	Širina: 54 mm Višina: 160 mm
Priklop okroglih vodnikov	1,5 - 35 mm <sup>2</sup>
Paketi	1 pc(s).
Neto teža	0,37 kg
Bruto teža	0,397 kg
Teža bakra (kg na kos)	0,081
Carinska tarifna številka	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV Mini-PLS busbar connection adaptor, 63 A, 690 V, 3-pole, round conductor connection 1,5-35 mm <sup>2</sup> , clamping area WH: 10x8 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK