

# Rittal – The System.

Faster – better – everywhere.



## SV 9614.100

## Mini-PLS adapter za komponente

State: 2.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9614.100 - Mini-PLS adapter za komponente

Največji nazivni tok od 12 A do 100 A.

## Features

Št. Modela	SV 9614.100
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Priključni kabli (AWG)	AWG 12
Nazivna delovna napetost	690 V, 3~
Maks. nazivni tok	25 A
Mere	Širina: 45 mm Višina: 160 mm
Podporne tirnice količina/višina	1 / 7,5 mm
Primerno za proizvajalca (tip)	ABB Eaton Schneider Electric Siemens MS116 PKZM0 bis 25 A PKZM01 bis 25 A PKE12 PKE32 bis 25 A GV2-P bis 25 A GV2-RT GV2-LE10 GV3 bis 25 A 3RV10 21 3RV20 21 bis 25 A 3RV10 11 3RV20 11
Paketi	1 pc(s).
Neto teža	0,25 kg

## Features

---

Bruto teža	0,29 kg
Teža bakra (kg na kos)	0,041
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 45x160 mm, support rail H: 7,5 mm

## Approvals

---

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK