

Rittal – The System.

Faster – better – everywhere.



SV 9627.000

Mini-PLS adapter za komponente

State: 6.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9627.000 - Mini-PLS adapter za komponente

Največji nazivni tok od 12 A do 100 A.

Features

Št. Modela	SV 9627.000
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Priključni kabli (AWG)	AWG 10
Nazivna delovna napetost	690 V, 3~
Maks. nazivni tok	40 A
Mere	Širina: 72 mm Višina: 160 mm
Podporne tirnice količina/višina	1 / 7,5 mm
Primerno za proizvajalca (tip)	Eaton PKZ2
Paketi	1 pc(s).
Neto teža	0,3 kg
Bruto teža	0,385 kg
Teža bakra (kg na kos)	0,046
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV Mini-PLS component adaptor, 40 A, 690 V, 3-pole, connection cable AWG 10, WH: 72x160 mm, support rail H: 7,5 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK
