



SV 9629.000 - Mini-PLS adapter za komponente

Največji nazivni tok od 12 A do 100 A.

Features

Št. Modela	SV 9629.000
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 9011
Priključni kabli (AWG)	35 mm ²
Nazivna delovna napetost	690 V, 3~
Maks. nazivni tok	100 A
Mere	Širina: 90 mm Višina: 160 mm
Primerno za proizvajalca (tip)	ABB Eaton Schneider Electric Siemens MS451 max. 40 A MS495 MS496 MS497 T1 T2 NZM 1 PKZM4 NS 80 GV3 3RV10 31 3RV1341/42
Paketi	1 pc(s).
Neto teža	0,694 kg
Bruto teža	0,759 kg

Features

Teža bakra (kg na kos)	0,23
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV Mini-PLS component adaptor, 100 A, 690 V, 3-pole, connection cable 35 mm ² , WH: 90x160 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK