

# Rittal – The System.

Faster – better – everywhere.



## SV 9629.010

## Mini-PLS adapter za komponente

State: 31.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9629.010 - Mini-PLS adapter za komponente

Največji nazivni tok od 12 A do 100 A.

## Features

Št. Modela	SV 9629.010
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 7035
Priključni kabli (AWG)	AWG 12
Nazivna delovna napetost	690 V, 3~
Maks. nazivni tok	25 A
Mere	Širina: 90 mm Višina: 160 mm
Podporne tirnice količina/višina	1 / 7,5 mm
Paketi	1 pc(s).
Neto teža	0,42 kg
Bruto teža	0,515 kg
Teža bakra (kg na kos)	0,041
Carinska tarifna številka	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Opis izdelka	SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 90x160 mm, support rail H: 7,5 mm

## Approvals

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK