

# Rittal – The System.

Faster – better – everywhere.



## SV 9630.000

# Mini-PLS podstavki varovalk za namestitev na montažne sponke

State: 27.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9630.000 - Mini-PLS podstavki varovalk za namestitev na montažne sponke

Nazivni tok 63 A



## Features

Št. Modela	SV 9630.000
Material	Poliamid Protipožarna zaščita v skladu z UL 94-V0
Barva	Ogrodje: RAL 9011 Pokrov: RAL 7035
Opomba	Pri tankih žičnih vodnikih je treba uporabljati kabelske čevlje s končnimi tulci.
Vrsta električne povezave	Box terminal
Vložki varovalk	D 02-E 18 (adaptor sleeve)
Nazivna delovna napetost	400 V
Maks. nazivni tok	63 A
Mere	Širina: 38 mm Višina: 160 mm
Priklop okroglih vodnikov	1,5 - 16 mm <sup>2</sup>
Paketi	1 pc(s).
Neto teža	0,3 kg

# Features

---

Bruto teža	0,316 kg
Teža bakra (kg na kos)	0,11
Carinska tarifna številka	85369095
ETIM 9	EC001644
ECLASS 8.0	27142120
Opis izdelka	SV Mini-PLS bus-mounting fuse base, D02-E18, 63 A, 400 V, 3-pole, round conductor connection 1,5-16 mm <sup>2</sup> , adaptor sleeve, including cover plate

# Approvals

---

Explanations

Declaration of conformity