

Rittal – The System.

Faster – better – everywhere.



SV 9635.373

Component adaptor

State: 16.1.2026 (Source: rittal.com/si-sl)



SV 9635.373 - Component adaptor 1-pole

For assembly of switchgear and protective gear.

Features

| | |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | SV 9635.373 |
| Design | L3 |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide Fire protection corresponding to UL 94 |
| Colour | RAL 7035 |
| Note | Different adaptor versions are required depending on the preferred phase connection The technical data may vary for UL applications |
| Rated current max. | 16 A |
| Rated operating voltage | 690 V (AC), 1~ |
| Number of poles | Single-pole |
| Connection cables (AWG) | AWG 14 |
| Length of connection cable | 100 mm |
| Support rails Qty/height | 1 / 10 mm |
| Support rail type | static |
| Dimensions | Width: 18 mm Height: 160 mm Depth: 35 mm |
| Packs of | 6 pc(s). |
| Net weight | 0.3 |
| Gross weight | 0.382 |
| Copper weight (kg per piece) | 0.009 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85369095 |
| EAN | 4028177934566 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|-----------------------------------------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
