

# Rittal – The System.

Faster – better – everywhere.



## SV 9666.530

## Modul zbiralnih sponk

State: 1.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9666.530 - Modul zbiralnih sponk za varnostne komponente

Za konfiguracijo podstavkov varovalk za montažo na vodila in NH ločilnike.

## Features

Št. Modela	SV 9666.530
Opis izdelka	Za izdelavo varnostnih elementov E18, E27, E33 in D-Switch ter NH ločilnikov velikosti 000 in 00 (3-polni, razdalja med središči 60 mm).
Material	Pokrov: polistiren Držalo: plastika, ojačana s steklenimi vlakni
Barva	RAL 7035
Obseg dobave	Sestavni deli
Mere	Širina: 500 mm Višina: 300 mm
Velikost	Širinske enote (WU) pri 250 mm: 2 Višinske enote (U) pri 150 mm: 2
Za model št.	3418.010 3427.010 3433.010 3431.020 3431.030 3431.035 9340.950
Za namestitev zbiralnih sponk	12 x 5/10 20 x 5/10 30 x 5/10
Paketi	1 pc(s).
Neto teža	0,6 kg
Bruto teža	1,04 kg
Carinska tarifna številka	85369095

# Features

---

ETIM 9	EC001896
ECLASS 8.0	27400610
Opis izdelka	SV Busbar module (ISV), 2 WU (500 mm), 2 U (300 mm)

---

# Approvals

---

Explanations	Declaration of conformity
	Declaration of conformity UK