

# Rittal – The System.

Faster – better – everywhere.



## SV 9666.570

# Modul tankega NH ločilnika

State: 8.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9666.570 - Modul tankega NH ločilnika

Za tanke NH ločilnike v velikostih od 00 do 3 (3-polni, razdalja med nosilci 100/185 mm).

## Features

Št. Modela	SV 9666.570
Opis izdelka	Za NH ločilnike velikosti 00 do 3 (3-polni, razdalja med središči 100/185 mm).
Material	Pokrov: polistiren Držalo: plastika, ojačana s steklenimi vlakni
Barva	RAL 7035
Obseg dobave	Sestavni deli
Opomba	Za zagotovitev nemotene kableske povezave je treba nad ali pod moduli NH ločilnikov namestiti modul za zaščito kontaktov ali modul zbiralnih sponk N/PE.
Mere	Širina: 250 mm Višina: 450 mm
Velikost	Širinske enote (WU) pri 250 mm: 1 Višinske enote (U) pri 150 mm: 3
Za velikost	3 x Gr. 00
Za model št.	9346.020 9346.030
Za namestitev zbiralnih sponk	40 x 10
Razmak med središči zbiralnih sponk	100 mm
Paketi	1 pc(s).
Neto teža	1,7 kg
Bruto teža	1,83 kg
Carinska tarifna številka	85369095
ETIM 9	EC001893

# Features

---

ECLASS 8.0	27400608
------------	----------

---

Opis izdelka	SV NH fuse-switch disconnecter module (ISV), 1 WU (250 mm), 3 U (450 mm), for 3 x size 00, (SV 9346XXX, 100 mm)
--------------	---

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---