

Rittal – The System.

Faster – better – everywhere.



SV 9666.583

NH slimline fuse-switch-disconnector module

State: 3.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.583 - NH slimline fuse-switch-disconnector module

For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar centre distance).

Features

| | |
|-------------------------------------|--|
| Model No. | SV 9666.583 |
| Product description | For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar centre distance). |
| Material | Cover: Polystyrene Holder: Fibreglass-reinforced plastic |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | In order to ensure problem-free cable connection, a contact hazard protection module or an N/PE busbar module must be installed above or below the NH slimline fuse-switch disconnector modules. |
| Dimensions | Width: 750 mm Height: 450 mm |
| Size | Width units (WU) @ 250 mm: 3 Height units (U) @ 150 mm: 3 |
| For size | 10 x Gr. 00 |
| To fit Model No. | 9346.020 9346.030 |
| To fit busbars | 40 x 10 |
| Centre-to-centre spacing of busbars | 100 mm |
| Packs of | 1 pc(s). |
| Net weight | 3,33 kg |
| Gross weight | 3,34 kg |

Features

| | |
|-----------------------|--|
| Customs tariff number | 85369095 |
| ETIM 9 | EC001893 |
| ECLASS 8.0 | 27400608 |
| Product description | SV NH fuse-switch disconnecter module (ISV), 3 WU (750 mm), 3 U (450 mm), for 10 x size 00, (SV 9346XXX, 100 mm) |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|