

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.610

## Konektorji zbiralnih sponk

State: 11.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.610 - Konektorji zbiralnih sponk

Za priklop zbiralnih sponk od 40 x 10 to 120 x 10 mm, brez vrtanja.

## Features

|   |  |
|---|--|
| Št. Modela  | SV 9677.610  |
| Opis izdelka  | Za povezovanje pravokotnih vodil brez vrtanja.   |
| Material  | E-Cu   |
| Površinska obdelava   | Pocinkano  |
| Za mere zbiralnih sponk (mm) /<br>Potrebna količina na zbiralno<br>sponko | 40 x 10 / 1<br>80 x 10 / 2<br>100 x 10 / 1   |
| Opomba  | Če uporabljate zbiralne sponke 100 x 10 mm, sta potrebni ena 9677.610 in ena 9677.620. |
| Za namestitvev zbiralnih sponk  | 40 x 10<br>80 x 10<br>100 x 10   |
| Mere  | Dolžina: 40 mm   |
| Paketi  | 1 pc(s).   |
| Neto teža   | 0,44 kg  |
| Bruto teža  | 0,5 kg   |
| Teža bakra (kg na kos)  | 0,407  |
| Carinska tarifna številka   | 74071000   |
| ETIM 9  | EC000713   |
| ECLASS 8.0  | 27400606   |
| Opis izdelka  | SV Busbar connector, for E-Cu 40/80/100x10 mm, L: 40 mm                                |

## Approvals

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---