

Rittal – The System.

Faster – better – everywhere.



SV 9677.610

Konektorji zbiralnih sponk

State: 5.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.610 - Konektorji zbiralnih sponk

Za priklop zbiralnih sponk od 40 x 10 to 120 x 10 mm, brez vrtanja.

Features

Št. Modela	SV 9677.610
Opis izdelka	Za povezovanje pravokotnih vodil brez vrtanja.
Material	E-Cu
Površinska obdelava	Pocinkano
Za mere zbiralnih sponk (mm) / Potrebna količina na zbiralno sponko	40 x 10 / 1 80 x 10 / 2 100 x 10 / 1
Opomba	Če uporabljate zbiralne sponke 100 x 10 mm, sta potrebni ena 9677.610 in ena 9677.620.
Za namestitvev zbiralnih sponk	40 x 10 80 x 10 100 x 10
Mere	Dolžina: 40 mm
Paketi	1 pc(s).
Neto teža	0,44 kg
Bruto teža	0,5 kg
Teža bakra (kg na kos)	0,407
Carinska tarifna številka	74071000
ETIM 9	EC000713
ECLASS 8.0	27400606
Opis izdelka	SV Busbar connector, for E-Cu 40/80/100x10 mm, L: 40 mm

Approvals

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity

Declaration of conformity UK