

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.885

# Tokovni transformator

State: 10.6.2026 (Source: [rittal.com/si-si](http://rittal.com/si-si))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.885 - Tokovni transformator

Za induktivno merjenje pretoka toka.

## Features

Št. Modela	SV 9677.885
Opis izdelka	Kompaktna zasnova brez spreminjanja globine vgradnje zaradi mehanske integracije v komponente (medosna razdalja 185 mm) omogoča zasnovo, ki prihrani prostor.
Material	Poliamid
Za velikost	3
Za model št.	9677.300 9677.310 9677.315 9677.340 9677.770 9677.780 9677.900
Nazivna vhodna moč	2,5 VA
Vrsta električne povezave	Box terminal
Insulation material (class)	H
Primary current	600 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Priklop okroglih vodnikov	2,5 - 4 mm <sup>2</sup>
Nazivna frekvenca	50 - 60 Hz
Paketi	1 pc(s).

# Features

Neto teža	0,168 kg
Bruto teža	0,17 kg
Carinska tarifna številka	85044087
ETIM 9	EC002048
ECLASS 8.0	27141146
Opis izdelka	SV current transformer 600 A/5 A for NH slimline fuse-switch disconnecter size 3 / connection and component adaptor (SV 9677.XXX)