

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.950 Tokovni transformator

State: 4.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.950 - Tokovni transformator

Za induktivno merjenje pretoka toka.

## Features

Št. Modela	SV 9677.950
Opis izdelka	Kompaktna zasnova brez spreminjanja globine vgradnje zaradi mehanske integracije v komponente (medosna razdalja 185 mm) omogoča zasnovo, ki prihrani prostor.
Material	Poliamid
Za model št.	9677.160 9677.165 9677.180 9677.260 9677.265 9677.280 9677.360 9677.365 9677.380 9677.930
Nazivna vhodna moč	1,5 VA
Vrsta električne povezave	Box terminal
Insulation material (class)	H
Primary current	250 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Priklop okroglih vodnikov	2,5 - 4 mm <sup>2</sup>
Nazivna frekvenca	50 - 60 Hz

# Features

Paketi	1 pc(s).
Neto teža	0,13 kg
Bruto teža	0,14 kg
Carinska tarifna številka	85043129
ETIM 9	EC002048
ECLASS 8.0	27141146
Opis izdelka	SV current transformer 250 A/5 A for NH slimline switch-disconnector size 1-3 / adaptor for RiLine Compact (SV 9677.XXX)