

Rittal – The System.

Faster – better – everywhere.



SV 9677.958

Tokovni transformator

State: 21.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.958 - Tokovni transformator

Za induktivno merjenje pretoka toka.

Features

Št. Modela	SV 9677.958
Opis izdelka	Kompaktna zasnova brez spreminjanja globine vgradnje zaradi mehanske integracije v komponente (medosna razdalja 185 mm) omogoča zasnovo, ki prihrani prostor.
Material	Poliamid
Za model št.	9677930
Nazivna vhodna moč	2,5 VA
Vrsta električne povezave	Box terminal
Insulation material (class)	H
Primary current	800 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Priklop okroglih vodnikov	2,5 - 4 mm ²
Nazivna frekvenca	50 - 60 Hz
Paketi	1 pc(s).
Neto teža	0,16 kg
Bruto teža	0,17 kg
Carinska tarifna številka	85043129
ETIM 9	EC002048
ECLASS 8.0	27141146

Features

Opis izdelka

SV current transformer 800 A/5 A for RiLine Compact 185 mm adaptor (SV 9677.930)