

Rittal – The System.

Faster – better – everywhere.



SV 9684.012

Zbiralne sponke E-Cu, perforirane

State: 10.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9684.012 - Zbiralne sponke E-Cu, perforirane



Features

Št. Modela	SV 9684.012
Opis izdelka	Zbiralne sponke z integriranimi perforacijami.
Material	E-Cu F30
Standardi	DIN EN 13 601
Prečni prerez	50 mm x 10 mm
Hole diameter	11,5 mm
Mere	Dolžina: 1.185 mm
Paketi	1 pc(s).
Neto teža	5,34 kg
Bruto teža	5,44 kg
Teža bakra (kg na kos)	5,34
Carinska tarifna številka	74071000
ETIM 9	EC001522
ECLASS 8.0	27370303
Opis izdelka	SV busbars E-Cu with integral punchings, length 1185 mm

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity UK