

# Rittal – The System.

Faster – better – everywhere.



## CS 9783.520

## Outdoor Basic enclosures

State: 4.4.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9783.520 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles



## Features

Model No.	CS 9783.520
Product description	Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.
Material	Aluminium AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and profile half-cylinder, lock BJ 20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy
Dimensions	Width: 800 mm Height: 1,200 mm Depth: 400 mm

# Features

---

Dimensions	Overall height: 1,355 mm Rain canopy width: 850 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 712 mm Clearance height: 1,112 mm Clearance depth: 349 mm Height base/plinth: 100 mm
------------	---

---

Type rating to UL 50E	Type 3R
-----------------------	---------

---

IP protection category to IEC 60529	IP 55
-------------------------------------	-------

---

IK Code	IK10
---------	------

---

Basic material	Aluminium
----------------	-----------

---

Packs of	1 pc(s).
----------	----------

---

Net weight	46 kg
------------	-------

---

Gross weight	48 kg
--------------	-------

---

Customs tariff number	94032080
-----------------------	----------

---

ETIM 9	EC000261
--------	----------

---

ECLASS 8.0	27180101
------------	----------

---