

# Rittal – The System.

Faster – better – everywhere.



## CS 9783.540

## Outdoor Basic enclosures

State: 4.3.2026 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9783.540 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles



## Features

|                     |                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.           | CS 9783.540                                                                                                                                                                                                                                                                                                                                                       |
| Product description | Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.                                                                                                                                                                                                                                                                     |
| Material            | Aluminium AlMg3                                                                                                                                                                                                                                                                                                                                                   |
| Surface finish      | Powder-coated<br>UV-resistant pure polyester                                                                                                                                                                                                                                                                                                                      |
| Colour              | RAL 7035                                                                                                                                                                                                                                                                                                                                                          |
| Supply includes     | Single-walled outdoor enclosure, fully preconfigured<br>Basic enclosure with gland plate, three-part<br>25 mm system punchings in the roof, base, front and in the enclosure depth<br>Front door(s) with door stay, swing lever handle and profile half-cylinder, lock BJ 20027<br>Transport plinth with screw-fastened trim panels front and rear<br>Rain canopy |
| Dimensions          | Width: 600 mm<br>Height: 800 mm<br>Depth: 400 mm                                                                                                                                                                                                                                                                                                                  |

# Features

|                                     |                                                                                                                                                                                                                               |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dimensions                          | Overall height: 955 mm<br>Rain canopy width: 650 mm<br>Rain canopy height: 55 mm<br>Rain canopy depth: 450 mm<br>Clearance width: 512 mm<br>Clearance height: 712 mm<br>Clearance depth: 349 mm<br>Height base/plinth: 100 mm |
| Type rating to UL 50E               | Type 3R                                                                                                                                                                                                                       |
| IP protection category to IEC 60529 | IP 55                                                                                                                                                                                                                         |
| IK Code                             | IK10                                                                                                                                                                                                                          |
| Basic material                      | Aluminium                                                                                                                                                                                                                     |
| Packs of                            | 1 pc(s).                                                                                                                                                                                                                      |
| Net weight                          | 29 kg                                                                                                                                                                                                                         |
| Gross weight                        | 34 kg                                                                                                                                                                                                                         |
| Customs tariff number               | 94032080                                                                                                                                                                                                                      |
| ETIM 9                              | EC000261                                                                                                                                                                                                                      |
| ECLASS 8.0                          | 27180101                                                                                                                                                                                                                      |