


# Rittal – The System.

Faster – better – everywhere.



## KX 1508.000

# Svorkovnicová skriňa KX, ocelový plech, bez príruby

State: 28.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1508.000 - Svorkovnicová skriňa KX, oceľový plech, bez príruby

The small enclosure KX, terminal box KX, without a gland plate allows for flexible interior installation while maintaining a high protection category.



## Features

Obj. č.	KX 1508.000
Materiál	Skriňa: oceľový plech Kryt: oceľový plech, polyuretánové penové tesnenie po celom obvode
Povrch	Skriňka a kryt: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skriňka s krytom Otočný mini uzáver
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 66

# Features

Type rating podľa UL 50E	Type 1 Type 3R Type 4 Type 12
Kód IK	IK08
Rozmery	Šírka: 400 mm Výška: 300 mm Hĺbka: 120 mm
Hrúbka materiálu krytu	1,25 mm
Hrúbka materiálu skrine	1,25 mm
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	4,696 kg
Brutto hmotnosť	4,701 kg
PCF per pack (cradle-to-gate)	34,63 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Popis výrobku	KX svorkovnicová skriňa, ŠxVxH: 400x300x120 mm, oceľový plech, bez montážnej dosky, s krytom, bez prírubovej dosky

# Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
-----------	--

# Approvals

---

Certificates

Protection category

---

Explanations

Manufacturer's declaration

Declaration of conformity

Declaration of conformity UK

PCF-declaration