

Rittal – The System.

Faster – better – everywhere.



KX 1531.000

Svorkovnicová skriňa KX, ocel'ový plech, s prírubou

State: 27.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1531.000 - Svorkovnicová skriňa KX, oceľový plech, s prírubou

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.



Features

Obj. č.	KX 1531.000
Materiál	Skriňa: oceľový plech Kryt: oceľový plech, polyuretánové penové tesnenie po celom obvode
Povrch	Skriňka a kryt: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skriňka s krytom Otočné mini uzávery Prírubové dosky z oceľového plechu vrátane tesnenia a upevňovacieho materiálu
Protection category NEMA	NEMA 1 NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 55
Type rating podľa UL 50E	Type 1 Type 12

Features

Kód IK	IK08
Rozmery	Šírka: 300 mm Výška: 200 mm Hĺbka: 120 mm
Hrúbka materiálu krytu	1,25 mm
Hrúbka materiálu skrine	1,25 mm
Prírubové dosky	Prírubová doska (horná + spodná), počet: 1 + 1
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	3,1 kg
Brutto hmotnosť	3,14 kg
PCF per pack (cradle-to-gate)	30,63 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Popis výrobku	KX svorkovnicová skriňa, ŠxVxH: 300x200x120 mm, oceľový plech, bez montážnej dosky, s krytom, prírubová doska

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Certificates	Protection category

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

PCF-declaration