

Rittal – The System.

Faster – better – everywhere.



BG 1558.510

Rozvodnicové skrinky BG

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1558.510 - Rozvodnicové skrinky BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Obj. č.	BG 1558.510
Materiál	Skriňa: oceľový plech Dvere: oceľový plech Okienko: polykarbonát, 4 mm
Povrch	Skriňa a dvere: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skrinka s dverami Priehľadové okno vo dverách Prírubová doska v dne skrine
Protection category NEMA	NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 65
Kód IK	IK08
Rozmery	Šírka: 400 mm Výška: 200 mm Hĺbka: 125 mm
Hrúbka materiálu skrine	1,25 mm
Hrúbka materiálu dverí	1,25 mm
Pozícia dverného dorazu	bottom
Počet nosných líšt	1
Uzáver	Vykonanie uzáveru: Rýchlouzáver vrátane plastových vložiek Počet uzáverov: 2
Základný materiál	Sheet steel
Balenie	1 pc(s).

Features

Netto hmotnosť	3,631 kg
Brutto hmotnosť	3,8 kg
Číslo colnej sadzby	94032080
ECLASS 8.0	27180101
Popis výrobku	BG Bus enclosure, WHD: 400x200x125 mm, Sheet steel, with gland plate in the base and support rails, Door with viewing window, hinged at bottom

Approvals

Approvals	Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity