

Rittal – The System.

Faster – better – everywhere.



KX 1576.000

E-box KX, ocel'ový plech

State: 22.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1576.000 - E-box KX, ocel'ový plech

The small enclosure KX, E-Box KX (sheet steel), offers remarkable ease of assembly and flexibility when selecting lock systems.



Features

Obj. č.	KX 1576.000
Materiál	Skriňa: ocel'ový plech Dvere: ocel'ový plech, po obvode polyuretánové penové tesnenie
Povrch	Skriňa a dvere: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Montážna doska: pozinkovaná
Farba	RAL 7035
Rozsah dodávky	Skriňa s dverami Montážna doska Otočný uzáver s uzatváracou vložkou Doppelbart 3 mm Pánty 180°
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 66

Features

Type rating podľa UL 50E	Type 1 Type 3R Type 4 Type 12
Kód IK	IK08
Rozmery	Šírka: 380 mm Výška: 300 mm Hĺbka: 155 mm
Rozmery montážnej dosky (Š x V)	365 mm x 275 mm
Hrúbka materiálu skrine	1,25 mm
Hrúbka materiálu dverí	1,25 mm
Hrúbka materiálu montážnej dosky	2 mm
Uzáver	Počet uzáverov: 1
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	6,6 kg
Brutto hmotnosť	6,635 kg
PCF per pack (cradle-to-gate)	39,42 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Popis výrobku	KX E-Box, ŠxVxH: 380x300x155 mm, ocelový plech, s montážnou doskou, jednodverový

Approvals

Approvals

Approvals

Bureau Veritas
DNV
Lloyds Register
UL + C-UL (listed)

Certificates

Protection category

Explanations

Manufacturer's declaration
Declaration of conformity
Declaration of conformity UK
PCF-declaration