

Rittal – The System.

Faster – better – everywhere.



BG 1583.520

Rozvodnicové skrinky BG

State: 26.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1583.520 - Rozvodnicové skrinky BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Obj. č.	BG 1583.520
Materiál	Skriňa: oceľový plech Dvere: oceľový plech Okienko: polykarbonát, 4 mm
Povrch	Skriňa a dvere: základná farba nanesená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skrinka s dverami Priehľadové okno vo dverách
Protection category NEMA	NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 65
Kód IK	IK08
Rozmery	Šírka: 200 mm Výška: 300 mm Hĺbka: 80 mm
Hrúbka materiálu skrine	1,25 mm
Hrúbka materiálu dverí	1,25 mm
Pozícia dverného dorazu	left
Počet nosných líšt	2
Výrezy (počet × Ø)	2
Uzáver	Vykonanie uzáveru: Otočný uzáver Počet uzáverov: 1 Vložka uzáveru: Doppelbart, 3 mm

Features

Zavedenie káblov (počet x Ø)	2 x M12 M20 M25
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	2,193 kg
Brutto hmotnosť	2,393 kg
Číslo colnej sadzby	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Popis výrobku	BG Bus enclosure, WHD: 200x300x80 mm, Sheet steel, with metric holes in the base and support rail, Door with viewing window, hinged on the left

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity