


# Rittal – The System.

Faster – better – everywhere.



## KX 1611.000

# Rozvodnicová skrinka KX, z oceľového plechu, s otočným mini uzáverom

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1611.000 - Rozvodnicová skrinka KX, z ocelového plechu, s otočným mini uzáverom

Wall-mounted enclosure made from sheet steel, with cover and viewing panel. Protection category IP 65/NEMA 12. For installing most brands of bus modules and sensors.



## Features

Obj. č.	KX 1611.000
Prevedenie	s presklenými dverami
Materiál	Skriňa: ocelový plech Kryt: ocelový plech, polyuretánové penové tesnenie po celom obvode Okienko: polykarbonát, 4 mm
Povrch	Skrinka a kryt: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skriňa so zaveseným vekom Presklené okienko v kryte Otočné mini uzávery
Protection category NEMA	NEMA 1 NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 65

## Features

Type rating podľa UL 50E	Type 1 Type 12
Kód IK	IK08
Rozmery	Šírka: 400 mm Výška: 300 mm Hĺbka: 155 mm
Hrúbka materiálu krytu	1,25 mm
Hrúbka materiálu skrine	1,25 mm
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	4,78 kg
Brutto hmotnosť	5 kg
PCF per pack (cradle-to-gate)	38,4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Popis výrobku	Rozvodnicová skrinka KX, ŠxVxH: 400x300x155 mm, oceľový plech, s uzavretou podlahou, s výklopným vekom a presklením

## Approvals

Approvals	Bureau Veritas C-UL DNV Lloyds Register
-----------	--

# Approvals

---

Explanations

Manufacturer's declaration  
Declaration of conformity  
Declaration of conformity UK  
PCF-declaration