


**Rittal – The System.**

Faster – better – everywhere.



**KX 1613.000**

**Rozvodnicová skrinka KX, z  
oceľového plechu, s otočným mini  
uzáverom**

State: 28.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1613.000 - Rozvodnicová skrinka KX, z ocelového plechu, s otočným mini uzáverom

Wall-mounted enclosure made from sheet steel, with cover and viewing panel. Protection category IP 65/NEMA 12. For installing most brands of bus modules and sensors.



## Features

Obj. č.	KX 1613.000
Prevedenie	s presklenými dverami
Materiál	Skriňa: ocelový plech Kryt: ocelový plech, polyuretánové penové tesnenie po celom obvode Okienko: polykarbonát, 4 mm
Povrch	Skrinka a kryt: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Skriňa so zaveseným vekom Presklené okienko v kryte Otočné mini uzávery
Protection category NEMA	NEMA 1 NEMA 12
Stupeň krytia IP podľa normy EN 60 529	IP 65

# Features

Type rating podľa UL 50E	Type 1 Type 12
Kód IK	IK08
Rozmery	Šírka: 800 mm Výška: 300 mm Hĺbka: 155 mm
Hrúbka materiálu krytu	1,25 mm
Hrúbka materiálu skrine	1,25 mm
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	8,39 kg
Brutto hmotnosť	8,84 kg
PCF per pack (cradle-to-gate)	49,3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Popis výrobku	Rozvodnicová skrinka KX, ŠxVxH: 800x300x155 mm, oceľový plech, s uzavretou podlahou, s výklopným vekom a presklením

# Approvals

Approvals	Bureau Veritas C-UL DNV Lloyds Register
-----------	--

# Approvals

---

Explanations

Manufacturer's declaration  
Declaration of conformity  
Declaration of conformity UK  
PCF-declaration