


Rittal – The System.

Faster – better – everywhere.



AX 2261.540

Nástenné skrinky AX, trojdielne

State: 28.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2261.540 - Nástenné skrinky AX, trojdielne

The delivery concept of the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.



Features

Obj. č.	AX 2261.540
Prevedenie	Nástenná skriňa IT
Materiál	Nástenný a otočný diel: ocelový plech, 1,5 mm Sklenené okno: jednovrstvové bezpečnostné sklo, 3 mm
Povrch	Štruktúrovaná prášková farba
Farba	Nástenný a otočný diel: RAL 7035 Presklené dvere: RAL 7035/7015 (bridlicovo šedá)
Rozsah dodávky	Stenový diel: prírubová doska uzavretá, horná a dolná Otočný diel s rastrom dierovania 25 mm v čelnom a zadnom ráme a dvoma 19" profilovými lištami, vpredu, pevná montáž Dizajnové presklené dvere Zámok stredného dielu: 3 mm Doppelbart Zámok dizajnových presklených dverí: bezpečnostný zámok 3524 E Komfortná rukoväť Mini
Výškové moduly	15 U
Rozmery	Šírka: 600 mm Výška: 745 mm Hĺbka: 473 mm

Features

Inštaláčn hbka	420 mm
Svetl rozmery	Svetl šrka: 502 mm Svetl vška: 684 mm
Hbka otočnho dielu	316 mm
Hbka nstennho dielu	135 mm
Počet uzverov	1
Zaažitelnos otočnho dielu (statick)	750 N
Load capacity of wall section (static)	250 N
Zkladny materil	Sheet steel
Uzver	Vykonanie uzveru: Komfortn rukov Mini Vloška uzveru: Bezpenostn vloška, zmok . 3524 E
Stupe krytia IP podla normy EN 60 529	IP 54 in conjunction with solid gland plate top and bottom
Balenie	1 pc(s).
Netto hmotnos	36,75 kg
Brutto hmotnos	38,1 kg
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
slo colnej sadzby	94032080
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180101
Popis vrobku	Nstenn skria AX, 3-dielna, ŠxVxH 600x745x473 mm, 15 U, bonica: uzavret prrubov doska hore a dole, s mini komfortnou rukovou

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
