


Rittal – The System.

Faster – better – everywhere.



SZ 2388.100 EMC tieniaca svorka

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2388.100 - EMC tieniaca svorka

Toolless quick assembly: Press the EMC shielding bracket against the cable shield and clip into the rail, diameter changes are compensated in full by the spring.

Features

Obj. č.	SZ 2388.100
Materiál	Oceľový plech
Povrch	Pozinkovaný
Priemer tienenia (min.)	3 - 10 mm
Balenie	10 pc(s).
Netto hmotnosť	0,11 kg
Brutto hmotnosť	0,123 kg
PCF per pack (cradle-to-gate)	0,5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002020
ETIM 8	EC002020
ECLASS 8.0	27141150
Popis výrobku	SZ EMC tieniaca svorka, pre priemer tienenia 3-10 mm