


Rittal – The System.

Faster – better – everywhere.



SZ 2460.650

Vložka uzáveru

State: 8.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2460.650 - Vložka uzáveru

Alternative lock inserts such as triangular, square, screwdriver, Daimler, Fiat, double-bit.

Features

Obj. č.	SZ 2460.650
Prevedenie	A
Materiál	Zinkový tlakový odliatok
Dĺžka	27 mm
Montáž v systéme rukovätí	Komfortná rukoväť AX Komfortná rukoväť Mini AX Štandardná rukoväť Ergoform-S Štandardná rukoväť Ergoform-S pre plastové rozvádzačové skrine KS
Uzáver	Vložka uzáveru: 6,5 mm trojhran (CNOMO)
Vhodné pre typ skrine	KX E-Box AX AX IT Operating housings AX AX plastic EB BG AE TE TP desk section and console TP pedestals One-piece console TP - Console cover One-piece console TP - Console door TP universal console CX one-piece console Console CX CX desk unit CX pedestal
Balenie	1 pc(s).
Netto hmotnosť	0,019 kg

Features

Brutto hmotnosť	0,021 kg
Číslo colnej sadzby	83016000
ETIM 9	EC000743
ETIM 8	EC000743
ECLASS 8.0	27409218
Popis výrobku	Uzatváracia vložka SZ, verzia A, zinkový tlakový odliatok, 6,5 mm trojuhran (CNOMO), D: 27 mm